

DSC-S600 Media Charts

*Number of images recorded on a single media (approx. no of shots)

| | Memory Stick Duo™ media | | | | Memory Stick PRO Duo™ media | | | | | Internal Memory |
|------------------------|-------------------------|------------|------------|-------------|-----------------------------|-------------|--------------|---------------|---------------|-----------------|
| | MSA-16A/AN | MSA-32A/AN | MSA-64A/AN | MSA-128A/AN | MSX-256 | MSX-512 | MSX-1GN | MSX-2GN | MSX-4GN | 32MB |
| Normal : Fine/Standard | | | | | | | | | | |
| 6M (2816 x 2112) | 5 / 9 | 10 / 19 | 21 / 39 | 42 / 79 | 77 / 142 | 157 / 290 | 322 / 592 | 680 / 1215 | 1305 / 2401 | 10 / 19 |
| 6M (2816 x 1872) 3:2 | 5 / 9 | 10 / 19 | 21 / 39 | 42 / 79 | 77 / 142 | 157 / 290 | 322 / 592 | 680 / 1215 | 1305 / 2401 | 10 / 19 |
| 3M (2048 x 1536) | 10 / 18 | 20 / 37 | 41 / 74 | 82 / 149 | 148 / 264 | 302 / 537 | 617 / 1097 | 1266 / 2250 | 2501 / 4447 | 20 / 37 |
| 2M (1920 x 1080) 16:9 | 16 / 30 | 33 / 61 | 66 / 123 | 133 / 246 | 238 / 446 | 484 / 907 | 988 / 1852 | 2025 / 3798 | 4002 / 7504 | 33 / 61 |
| 2M (1632 x 1224) | 16 / 30 | 33 / 61 | 66 / 123 | 133 / 246 | 238 / 446 | 484 / 907 | 988 / 1852 | 2025 / 3798 | 4002 / 7504 | 33 / 61 |
| VGA (640 x 480) | 97 / 243 | 196 / 491 | 394 / 985 | 790 / 1975 | 1428 / 3571 | 2904 / 7261 | 5928 / 14821 | 12154 / 30385 | 24014 / 60036 | 196 / 491 |
| MPEG MOVIE (sec) | | | | | | | | | | |
| VX FINE | - | - | - | - | 177 | 362 | 740 | 1518 | 3001 | - |
| VX Standard | 42 | 87 | 176 | 354 | 642 | 1307 | 2667 | 5469 | 10806 | 87 |
| Video mail | 672 | 1362 | 2739 | 5493 | 10281 | 20825 | 42262 | 87505 | 172900 | 1362 |

File size of the movie is limited to approximately 2GB. Recording will automatically stop when file size reaches this limit.

*Battery Life / No. of Shots

- CIPA

Supplied Battery (Alkaline)

| | Memory Stick® media | |
|-------------|---------------------|-------------|
| Still image | Approx. 65 min. | Approx. 130 |

Optional Battery (NH-AA-2DB)

| | Memory Stick® media | |
|-------------|---------------------|-------------|
| Still image | Approx. 230 min. | Approx. 460 |

Image quality: "FINE".

The LCD screen is turned on.

Shooting once every 30 seconds.

The zoom is switched alternately between WIDE and TELE ends.

The flash strobos once every two times.

The power turns on and off once every ten times.

Note: Actual numbers may differ based on the condition of use.